




Barrier-free sterilization

Can kill harmful substances bacteria through obstacles



LED UV Germicidal Lamp

Features Description

- 1.360 degree High-intensity UVC disinfection, no ozone.
- 2. Built-in Radar Sensor, easy to protect people.
- 3. Rapid sterilization, much safe and efficient.
- 4. Aluminum material for heat dissipation, longer life.
- 5.Smart remote control, One/two/Four hours timing control, easy to use.
- 6.Eliminate all kinds of bacterial and odors in large spaces.

Warning

1. Please switch off the power during installation! 2.Please turn off the bulb before approaching it! 3. It's better to use the Remote controller for operation! 4. When it's working, do not expose your eyes and skin under the bulb! People, animals and plants must leave the scene!

Applications

1. Widely used in the high-efficiency disinfection of large-scale indoor places, such as big room, office, hotel, warehouse, hospital, gym, store, studio etc.


Model	Input Voltage	Lamp Size	Weight
ACL80-03-UCR	AC100-130V	φ170*332 mm /φ6. 70*13. 07 in	2. 2kg

• 15344a Valley Blvd City of Industry CA 91746 **&** +1 201 969 5019 / +1 323 616 7060

robert@nssled.com



Packaging unit (Pieces/Unit)	Dimensions	Gross weight
Small box 1	14.57*8.46*8.66in	2.2kg
Outer Carton 4	14.96*17.52*18.11in	12kg



The package box will be used according to the package condition



• 15344a Valley Blvd City of Industry CA 91746 +1 201 969 5019 / +1 323 616 7060

robert@nssled.com



LED UV Germicidal Lamp

Eliminate Viruses and Bacteria





Features Description

1.360 degree disinfection, no ozone, much safer. 2. High-intensity UVC ultraviolet bacteriostasis. 3.30 minutes rapid sterilization, safe and efficient. 4. Eliminate all kinds of bacterial and odors in large spaces.

5. Aluminum material for heat dissipation, longer life. 6.Smart remote control (optional), timing control, easy to use.

Warning

1.Please switch off the power during installation! 2. Please turn off the bulb before approaching it! 3. It's better to use the Remote controller for operation! 4. When it's working, do not expose your eyes and skin under the bulb! People, animals and plants must leave the scene!

Applications

1. Widely used in the high-efficiency disinfection of large-scale indoor places. such as canteens, homes, hospitals, gyms, store stores, etc.


Model	Input Voltage	Operating frequency	Base	Lamp Size	N.W
ACL30-02-U	AC100-277V	50/60Hz	E26/E27	7.16*2.56 in	345g
ACL30-02-UC	Lamp 100-277V, Remote control100-130V	50/60Hz	E26/E27	12.08*4.13*2.56 in	675g

15344a Valley Blvd City of Industry CA 91746 +1 201 969 5019 / +1 323 616 7060

- **interm** robert@nssled.com



Model	Packaging unit (Pieces/Unit)	Dimensions	Gross weight
ACL30-02-U	Small box 1	8.3*3.9*3.9in	0.31kg
	Outer Carton 40	20.9*17.3*16.9in	16.5kg
	Small box 1	12.2*4.3*3.9in	0.7kg
ACL30-02-UC	Outer Carton 24	24.8*17.7*12.2in	18kg



The package box will be used according to the package condition



• 15344a Valley Blvd City of Industry CA 91746 +1 201 969 5019 / +1 323 616 7060

robert@nssled.com

order@newsunshine.net S www.nssled.com www.nsslighting.com

2





LED UV Germicidal Lamp

Features Description

1.No ozone, much safer.

- 2. High-intensity UVC ultraviolet bacteriostasis.
- 3.Small size, easy installation and transportation..
- 4.30 minutes rapid sterilization, deep efficient adsorption.
- 5.Eliminate peculiar smell in narrow and confined spaces.

6.Radar Sensor (optional), more protection for people during disinfection progress

7.Smart remote control (optional), timing control

Warning

1. Please switch off the power during installation! 2. Please turn off the bulb before approaching it! 3. When it's working, do not expose your eyes and skin under the bulb! People, animals and plants must leave the scene!

4. At any time, don't touch the light-emitting part of the lamp with your hands or other objects to avoid damage to the LEDs caused by static electricity

Applications

1. Widely used for high-level disinfection of bedrooms, kitchens, toilets, wardrobes, and other small space areas.


Model	Input Voltage	Operating frequency	Dimension	Base	N.W	Package
ACL5-01-U	100-265V	50/60Hz	Dia 2.56*3.38inch(Bulb)	E26/E27	0.19lb(Bulb)	Box size: L7.17*W4.25*H4.92inch
ACL5-01-UC	100-265V	50/60Hz	Dia 2.56*3.38inch(Bulb)	E26/E27	0.19lb(Bulb)	Box size: L7.17*W4.25*H4.92inch

15344a Valley Blvd City of Industry CA 91746 +1 201 969 5019 / +1 323 616 7060


interm robert@nssled.com



Model	Packaging unit (Pieces/Unit)	Dimensions	Gross weight
ACL5-01-U	Small box 1	3.5*3.5*5.1in	0.13kg
	Outer Carton 108	21.6*21.6*16.1in	14kg
Small box 1		7.5*4.3*5.1in	0.7kg
ACL5-01-UC	Outer Carton 24	22.0*17.7*16.1in	18kg



The package box will be used according to the package condition



• 15344a Valley Blvd City of Industry CA 91746 +1 201 969 5019 / +1 323 616 7060

robert@nssled.com





LED UV Germicidal Lamp

Features Description

- 1.No ozone, much safer.
- 2. High-intensity UVC ultraviolet bacteriostasis.
- 3.5V input rechargeable, Charge 1H and last 2H.

4. Eliminate peculiar smell in narrow and confined spaces.

5.IR remote control, switching and timing

(3 gears timing control).

6.Portable, swipe back and forth 5 times, fast disinfectio.

Warning

1. Please switch off the power during installation! 2. Please turn off the bulb before approaching it! 3. It's better to use the Remote controller for operation! 4. When it's working, do not expose your eyes and skin under the bulb! People, animals and plants must leave the scene!

Applications

1. Widely used for high-level disinfection of living room, bedroom, bathroom, kitchen, clothing, toys, shoe cabinet, wardrobe, storage box, backpack, car, pet nest, and other small space areas.


Model	Input Voltage	Dimension	Accessories	Package
ACL5-02-UC	DC5V, 1A	Dia 2.56*4.6inch(with hook)	Remote control*1,USB Cable*1	1pcs/Box, Box Size: 3.43*3.43*4.92inch GW: 0.38lb
ACL5-03-UC	DC5V, 1A	Dia 2.56*4.6inch(with hook)	Remote control*1,USB Cable*1	1pcs/Box, Box Size: 3.43*3.43*4.92inch GW: 0.38lb

15344a Valley Blvd City of Industry CA 91746 **** +86-769-88004885 +86-13826588764

interm robert@nssled.com



Packaging unit (Pieces/Unit)	Dimensions	Gross weight
Small box 1	3.42*3.42*4.92in	0.173kg
Outer Carton 75	17.91*17.91*15.94ir	14kg



The package box will be used according to the package condition



• 15344a Valley Blvd City of Industry CA 91746 +1 201 969 5019 / +1 323 616 7060

robert@nssled.com

UVC Disinfection Box

Features Description

1. With UV tubes in two sides of the Box, 360 degree circulation disinfection.

2.Can be a power supply for other devices by USB charging during disinfection process.

3. Aromatherapy function to provide fragrance for the disinfection object.

4. Indicator lights and voice prompts to ensure safe and correct use

5.Safe and portable with DC5V supply .

6.Large capacity disinfection, appliable for up to 6 inch mobile phones, watches, toothbrushes, masks, underwear, jewelry and other small objects.

Warning

1.Keep the Box far from flame, water and corrosive chemicals.

2.Do not clean the Box with organic solvent.

3.Do not stare at the disinfection box for a long time.

How to use

1.Connect the power supply cable, put the object into the disinfection box, press the Sterilize button, then the object begins to be sterilized, and the Indicator lights is showing the disinfection progress. After 3 minutes, disinfection is completed and the UV tubes will turn off automatically. If you like aromatherapy, put essential oil in the aroma inlet, then press the Incense button anytime.

Model	Input Voltage	Dimension	Ultraviolet wavelength	Power (Incense)	Power (sterilize)	Max power	Weight	Max capacity	Package
DCB-001-NI	DC5V, 2A	7.76*6.02*1.93inch	253.7nm	1W	2W	9W	0.36kg	6 inch mobile phone	30pcs/CTN, GW: 13.2kg/CTN, 19.5*16.5*13in

15344a Valley Blvd City of Industry CA 91746 **&** +1 201 969 5019/+1 323 616 7060

robert@nssled.com

order@newsunshine.net 🚯 www.nssled.com www.nsslighting.com

1



Super sterilization and disinfection box

Multiple Applications












Packaging unit (Pieces/Unit)	Dimensions	Gross weight
Small box 1	6.30*2.36*8.0inch	0.36kg
Outer Carton 30	19.5*16.5*13inch	13.2kg



The package box will be used according to the package condition



• 15344a Valley Blvd City of Industry CA 91746 +1 201 969 5019 / +1 323 616 7060

robert@nssled.com